

Adapter NPFV-AF-G14-N14-MF

Part number: 563397

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	6 mm
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pneumatic connection 1	G1/4
Pneumatic connection 2	1/4 NPT
Note on materials	RoHS-compliant
Adapter material	High-alloy stainless steel
Seals material	NBR