

Pressure regulator MS9-LR-NG-D5-DI-AG-PSI-AS

Part number: 564140

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 9 |
| Series | MS |
| Actuator lock | can be closed with accessories |
| Mounting position | Any |
| Structural design | Directly controlled diaphragm regulator |
| Controller function | Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function |
| Symbol | 00991536 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 1 bar ... 20 bar |
| Pressure regulation range | 0.5 bar ... 4 bar |
| Max. pressure hysteresis | 0.4 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 7 according to ISO 14644-1 |
| Storage temperature | -10 °C ... 60 °C |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1400 g |
| Type of mounting | With accessories |
| Covering material | PA-reinforced |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast aluminum |
| Material of mounting bracket | Die-cast aluminum |
| Housing material | Die-cast aluminum |
| Module connector material | Die-cast aluminum |
| Diaphragm material | NBR |

| Feature | Value |
|-----------------------|--------------------------------------|
| Valve tappet material | Wrought aluminum alloy NBR POM |