

Branching module MS9-FRM-G-VS-Y

Part number: 564147

FESTO



 General operating condition

Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	Any
Structural design	Branching module
Symbol	00991510
Operating pressure	0 bar ... 12 bar
Operating voltage range AC	0 V ... 250 V
DC operating voltage range	0 V ... 125 V
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Storage temperature	-10 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	1100 g
Type of mounting	Alternatively: Front panel mounting In-line installation With accessories
Pneumatic connection 3	G1
Pneumatic connection 4	G1
Covering material	PA-reinforced
Note on materials	RoHS compliant
Material of sub-base	Die-cast aluminum
Material of mounting bracket	Die-cast aluminum
Housing material	Die-cast aluminum
Module connector material	Die-cast aluminum