

Branching module MS9-FRM-NG-VS

Part number: 564148

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | 9 |
| Series | MS |
| Mounting position | Any |
| Structural design | Branching module |
| Symbol | 00991510 |
| Operating pressure | 0 bar ... 20 bar |
| Operating voltage range AC | 0 V ... 250 V |
| DC operating voltage range | 0 V ... 125 V |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Lubricated operation possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 7 according to ISO 14644-1 |
| Storage temperature | -10 °C ... 60 °C |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1000 g |
| Type of mounting | Alternatively: Front panel mounting In-line installation With accessories |
| Pneumatic connection 3 | 1 NPT |
| Pneumatic connection 4 | 1 NPT |
| Covering material | PA-reinforced |
| Note on materials | RoHS compliant |
| Material of sub-base | Die-cast aluminum |
| Material of mounting bracket | Die-cast aluminum |
| Housing material | Die-cast aluminum |
| Module connector material | Die-cast aluminum |