

Push-in X connector QBX-1/2T-U

Part number: 564783

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 8.992 mm |
| Mounting position | Any |
| Design | X-Shape |
| Pack size | 5 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Lubricated operation possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 36.997 g |
| Pneumatic connection 1 | For pneumatic tubing outside diameter 1/2" |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 1/2" |
| Ambient temperature Fahrenheit | 32 °F ... 140 °F |
| Releasing ring color | Gray |
| Note on materials | RoHS compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | high-alloy stainless steel |