

Blanking plug QBC-3/8H-U

Part number: 564788

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Mounting position	Any
Design	Blanking plug
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C ... 60 °C
Product weight	2.013 g
Pneumatic connection 1	Push-in sleeve Ø 3/8"
Ambient temperature Fahrenheit	32 °F ... 140 °F
Note on materials	RoHS-compliant
Housing material	POM