

# Manifold rail VABM-L1-10AS-M5-14

Part number: 566532

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value  |
|--|--|
| Width dimension                              | 10.5 mm  |
| Max. no. of valve positions                  | 16   |
| Operating pressure                           | -0.09 MPa ... 1 MPa                              |
| Operating pressure                           | -0.9 bar ... 10 bar                              |
| Certification                                | RCM compliance mark<br>c UL us - Recognized (OL) |
| Corrosion resistance class (CRC)             | 2 - Moderate corrosion stress                    |
| LABS (PWIS) conformity                       | VDMA24364-B1/B2-L                                |
| Max. tightening torque for DIN rail mounting | 1.5 Nm   |
| Max. tightening torque for valve mounting    | 0.45 Nm  |
| Max. tightening torque for wall mounting     | 3 Nm   |
| Product weight                               | 122 g  |
| Pneumatic connection 1                       | M5   |
| Pneumatic connection 3                       | M5   |
| Pneumatic connection 5                       | M5   |
| Note on materials                            | RoHS-compliant                                   |
| Manifold rail material                       | Wrought aluminum alloy                           |