


# Electrical sub-base VAVE-L1-1VS3-LP

Part number: 566719

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark suppression
Signal status display	LED
Nominal operating voltage DC	12 V
Surge resistance	0.8 kV
Contamination level	3
Extended ambient temperature	-5 - 60 °C
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 50 °C
Mounting position	Any
Product weight	1.6 g
Electrical connection	2-pin Socket
Protective earth connection	Not available
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA