


# Electrical sub-base VAVE-L1-1S2-LR

Part number: 566720

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value  |
|--|--|
| Reverse polarity protection                  | for operating voltage                          |
| Additional functions                         | Spark suppression<br>Holding current reduction |
| Signal status display                        | LED  |
| Nominal operating voltage DC                 | 24 V   |
| Surge resistance                             | 0.8 kV   |
| Contamination level                          | 3  |
| Certification                                | RCM compliance mark                            |
| CE marking (see declaration of conformity)   | As per EU EMC directive                        |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC                     |
| Corrosion resistance class (CRC)             | 0 - No corrosion stress                        |
| LABS (PWIS) conformity                       | VDMA24364-B1/B2-L                              |
| Degree of protection                         | IP40   |
| Ambient temperature                          | -5 °C ... 60 °C                                |
| Mounting position                            | Any  |
| Product weight                               | 1.5 g  |
| Electrical connection                        | 2-pin<br>Socket                                |
| Protective earth connection                  | Not available                                  |
| Type of mounting                             | Clip   |
| Housing colour                               | Black  |
| Note on materials                            | RoHS-compliant                                 |
| Housing material                             | PA   |