

Electrical sub-base VAVE-L1-1VL1-LP

Part number: 566722

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark suppression
Signal status display	LED
Nominal operating voltage DC	12 V
Surge resistance	0.8 kV
Contamination level	3
Extended ambient temperature	-5 - 60 °C
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 50 °C
Mounting position	Any
Product weight	4.6 g
Connection cross section	0.14 mm ²
Electrical connection	Flying lead
Cable length	0.5 m
Wire ends	Cable end sleeve
Protective earth connection	Not available
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA