


Limit switch box SRAP-M-CA1-GR270-1-A-T2P20

Part number: 568246

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Rectangular
Based on norm	VDI/VDE 3845 (NAMUR)
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	Rotation angle
Measuring principle	Magnetic Hall
Ambient temperature	-20 °C ... 80 °C
Analog output	4 - 20 mA
Repetition accuracy analog output in ± °	1 deg
Short-circuit protection	yes
Overload protection	Available
DC operating voltage range	15 V ... 30 V
Idle current	12 mA ... 20 mA
Reverse polarity protection	for all electrical connections
Electrical connection	Screw terminal Plug-in
Closable nominal conductor cross-section	2.5 mm ²
Cable fitting	M20
Approved cable diameter	5 mm ... 13 mm
Max. cable length	30 m
Mounting position	Any
Product weight	1000 g
Housing material	Wrought aluminum alloy
Position indicator	Red/green
Setting options	Teach-in Teach-in via electrical connection
Angle detection setting range	0 deg ... 270 deg
Degree of protection	IP65
Insulation voltage	50 V
Surge resistance	0.8 kV
Protection class	III
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L

Feature	Value
Contamination level	3