

# Cable fitting NETC-M-M20-KA

Part number: 568279

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Ambient temperature	-20 °C ... 100 °C
Degree of protection	IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE marking (see declaration of conformity)	As per EU RoHS directive
Size	M20x1.5
Cable diameter	5 mm ... 13 mm
Color	Silver
Material for cable connector	PA
Seals material	EPDM
Product weight	103 g
Pack size	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	3 - High corrosion stress