

# Plastic tubing PUN-V0-14X2-SW-C

Part number: 570351

FESTO



 General operating condition

## Data sheet

Feature	Value
Outside diameter	14 mm
Bending radius relevant for flow rate	70 mm
Inside diameter	9.8 mm
Min. bending radius	45 mm
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 MPa ... 0.6 MPa
Operating pressure for entire temperature range	-0.95 bar ... 6 bar
Operating pressure for entire temperature range	-13.775 psi ... 87 psi
Temperature-dependent operating pressure	-0.095 MPa ... 0.9 MPa
Temperature-dependent operating pressure	-0.95 bar ... 9 bar
Temperature-dependent operating pressure	-13.775 psi ... 130.5 psi
Information on operating pressure	Water: max. 0.6 MPa at max. 50 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Material fire test	UL94 V-0 (3mm) UL94 V-2 (0.75mm)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C ... 60 °C
Note on ambient temperature	unpressurised use up to 90°C
Product weight by length	0.096 kg/m
Pneumatic connection	For plug connection outside diameter 14 mm
Color	Black
Information on color	Deviates from the standard color due to flame protection
Shore hardness	D 54 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)