

Plastic tubing PUN-V0-16X2-SW

Part number: 570767

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Outside diameter | 16 mm |
| Bending radius relevant for flow rate | 90 mm |
| Inside diameter | 11.8 mm |
| Min. bending radius | 50 mm |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 MPa ... 0.6 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 6 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 87 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 0.9 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 9 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 130.5 psi |
| Information on operating pressure | Water: max. 0.6 MPa at max. 50 °C |
| Certification | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0527 00 |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Material fire test | UL94 V-0 (3mm) UL94 V-2 (0.75mm) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -35 °C ... 60 °C |
| Note on ambient temperature | unpressurised use up to 90°C |
| Product weight by length | 0.122 kg/m |
| Pneumatic connection | For plug connection outside diameter 16 mm |
| Color | Black |
| Information on color | Deviates from the standard color due to flame protection |
| Shore hardness | D 54 +/-3 |
| Note on materials | RoHS-compliant |
| Material of pneumatic tubing | TPE-U(PU) |