

Retainer VMPA1-FTI-10

Part number: 572542

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	10
Mounting position	Any
Pack size	10
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Operating pressure	-13.05 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 40 °C
Temperature of medium	-5 °C ... 60 °C
Ambient temperature	-5 °C ... 60 °C
Product weight	0.07 g
Type of mounting	Clamped
Note on materials	RoHS compliant
Retainer bracket material	POM