

# Push-in T-connector QBMT-1/4T-U

Part number: 573069

FESTO



 General operating condition

## Data sheet

| Feature   | Value   |
|---|---|
| Size  | Mini  |
| Nominal width                                   | 5.004 mm                                      |
| Mounting position                               | Any   |
| Design  | T-shape                                       |
| Pack size                                       | 10  |
| Structural design                               | Push-pull principle                           |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa                          |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar                          |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi                       |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media        | Lubricated operation possible                 |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                      |
| LABS (PWIS) conformity                          | VDMA24364 Zone III                            |
| Ambient temperature                             | 0 °C ... 60 °C                                |
| Product weight                                  | 6.01 g  |
| Pneumatic connection 1                          | For pneumatic tubing outside diameter 1/4"    |
| Pneumatic connection 2                          | for pneumatic tubing outer diameter 1/4"      |
| Ambient temperature Fahrenheit                  | 32 °F ... 140 °F                              |
| Releasing ring color                            | Gray  |
| Note on materials                               | RoHS compliant                                |
| Housing material                                | PBT   |
| Releasing ring material                         | POM   |
| Material of tubing seal                         | NBR   |
| Material of tube retaining claw                 | high-alloy stainless steel                    |