

# Manifold rail VABM-L1-10G-G18-6-GR

Part number: 573425

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Width dimension	10.5 mm
Mounting position	Any
Max. no. of valve positions	6
Certification	c UL us - recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 60 °C
Product weight	397 g
Pilot air port 12/14	M5
Pilot exhaust air port 82/84	M5
Pneumatic connection 1	G1/8
Pneumatic connection 3	G1/8
Pneumatic connection 5	G1/8
Note on materials	RoHS compliant
Manifold rail material	Wrought aluminum alloy