

Manifold rail VABM-L1-14W-G14-9-GR

Part number: 573505

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width dimension	16 mm
Mounting position	Any
Max. no. of valve positions	9
Certification	c UL us - recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Storage temperature	-20 °C ... 60 °C
Product weight	1344 g
Pilot air port 12/14	M5
Pilot exhaust air port 82/84	M5
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/8
Pneumatic connection 3	G1/4
Pneumatic connection 4	G1/8
Pneumatic connection 5	G1/4
Note on materials	RoHS compliant
Manifold rail material	Wrought aluminum alloy