

Power supply module VMPAL-SP-QS8

Part number: 573645

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--|
| Width | 23.2 mm |
| Length | 107.3 mm |
| Integrated function | With electrical manifold module |
| Valve manifold design | Valve sizes can be mixed |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Pilot pressure MPa | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 50 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 8 mm |
| Note on materials | RoHS-compliant |
| Power supply module material | Wrought aluminum alloy PA-reinforced |