

# Power supply module VMPAL-SP-QS5/16"

Part number: 573646

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Width	23.2 mm
Length	107.3 mm
Integrated function	With electrical interlinking module
Valve manifold design	Interchangeable valve sizes
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	50 g
Pneumatic connection 1	For pneumatic tubing outside diameter 5/16"
Note on materials	RoHS compliant
Power supply module material	Wrought aluminum alloy PA-reinforced