

# Electrical sub-base VAVE-L1-1R8-LR

Part number: 573920

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark suppression Holding current reduction
Signal status display	LED
Nominal operating voltage DC	24 V
Surge resistance	0.8 kV
Contamination level	3
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Product weight	3.2 g
Electrical connection	M8 / - Plug/socket
Protective earth connection	Not available
Type of mounting	On air solenoid valve with self-tapping screw
Housing colour	Black
Note on materials	RoHS-compliant
Cover material	PA
Seals material	EPDM
Housing material	PA
Material of screws	Tempered steel