


# Electrical sub-base VAVE-L1-1VK8-LP

Part number: 573943

FESTO



## Data sheet

 General operating condition

Feature	Value
Cable characteristic	for static applications
Reverse polarity protection	Bipolar
Additional functions	Spark suppression
Signal status display	LED
Nominal operating voltage DC	12 V
Surge resistance	0.8 kV
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	47 g
Electrical connection	Rectangular design/open end
Cable design	2 x 0.25 mm <sup>2</sup>
Cable diameter	3.4 mm
Cable diameter tolerance	± 0.1 mm
Cable length	2.5 m
Wire ends	Cable end sleeve
Protective earth connection	Not available
Type of mounting	On air solenoid valve with self-tapping screw
Housing colour	Black
Note on materials	RoHS-compliant
Cover material	PA
Seals material	EPDM
Housing material	PA
Material of cable sheath	TPV
Material of screws	Tempered steel