

Electrical sub-base VAVE-L1-1VK9-LP

Part number: 573944

FESTO



 General operating condition

Data sheet

Feature	Value
Cable characteristic	For static applications
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V
Surge resistance	0.8 kV
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	92 g
Electrical connection	Rectangular design/open end
Cable design	2 x 0.25 mm ²
Cable diameter	3.4 mm
Cable diameter tolerance	± 0.1 mm
Cable length	5 m
Wire ends	Wire ferrule
Protective earth connection	Not available
Type of mounting	On air solenoid valve with self-tapping screw
Housing colour	Black
Note on materials	RoHS compliant
Cover material	PA
Seals material	EPDM
Housing material	PA
Material of cable sheath	TPV
Material of screws	Quenched and tempered steel