


Plug NECU-S1W9-C2-APB

Part number: 574589

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	40 mm
Height	72 mm
Length	17 mm
Type of mounting	4-40 UNC-2B
Product weight	43 g
Fieldbus interface	Sub-D, 9-pin, plug
Electrical connection 1	9-pin Sub-D plug
Electrical connection 2	IDC terminal
Baud rate	12 Mbit/s
Approved cable diameter	8 mm
Approved cable diameter	8 mm
Connection cross section	0.64 mm ²
Degree of protection	IP20
Ambient temperature	-25 °C ... 60 °C
Storage temperature	-25 °C ... 80 °C
Relative air humidity	75% at 25 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	Metalized plastic