

Plug NECU-M-S-A12G4-IS

Part number: 575719

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Based on norm	EN 61076-2-101
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Mounting position	Any
Product weight	38 g
Electrical connection	4-pin Spring-loaded terminal M12x1 Straight plug
Plug coding	A
DC operating voltage range	0 V ... 30 V
Current rating at 40° C	4 A
Approved cable diameter	4 mm ... 8 mm
Connection cross section	0.14 mm ² ... 0.5 mm ²
Degree of protection	IP65 IP67
Ambient temperature	-40 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Contamination level	3
Corrosion resistance class (CRC)	0 - No corrosion stress
Housing material	Die-cast zinc Nickel-plated
Material of pin contacts	Bronze Gold-plated