

Mounting kit SAMH-S-N8-L-MK

Part number: 575816

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	for T-slot
Note on materials	RoHS-compliant
Ambient temperature	-40 °C ... 85 °C
Type of mounting	Engaging Screwed tightly Can be inserted in slot from above
Max. tightening torque	0.6 Nm
Product weight	1.91 g
Cover cap material	PA
Terminal block material	High-alloy steel
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L