

Plug NECC-S1G9-C2-M

Part number: 576031

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Height	39.4 mm
Length	58 mm
Product weight	24 g
Fieldbus interface	Sub-D, 9-pin, socket
Electrical connection	9-pin/9-pin Sub-D/screw terminal
Baud rate	1 Mbit/s
Approved cable diameter	8 mm
Approved cable diameter	8 mm
Degree of protection	IP40
Ambient temperature	-20 °C ... 70 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress