

# Manifold block VABM-B10-20E-N38-3

Part number: 576352

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Width dimension                  | 22 mm                         |
| Mounting position                | Any                           |
| Max. no. of valve positions      | 3                             |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L             |
| Product weight                   | 866 g                         |
| Type of mounting                 | With through-hole             |
| Pilot air port 12                | 1/8 NPT                       |
| Pilot air port 14                | 1/8 NPT                       |
| Pneumatic connection 1           | 3/8 NPT                       |
| Pneumatic connection 3           | 3/8 NPT                       |
| Pneumatic connection 5           | 3/8 NPT                       |
| Note on materials                | RoHS-compliant                |
| Manifold rail material           | Wrought aluminum alloy        |