

End plate VMPAC-EPL-MP-SD25-O

Part number: 576558

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Operating pressure	-0.9 bar ... 8 bar
Pilot pressure	3 bar ... 8 bar
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	246 g
Pneumatic connection 3	G3/8
Pneumatic connection 5	G3/8
Note on materials	RoHS-compliant
Housing material	PA-reinforced