

Push-in sleeve NPQH-D-S4-E-P10

Part number: 578317

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal width	2 mm
Mounting position	Any
Design	Straight design
Pack size	10
Symbol	00997424
Operating pressure for entire temperature range	-0.095 MPa ... 2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 20 bar
Operating pressure for entire temperature range	-13.775 psi ... 290 psi
Information on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certificate issuing authority	NSF C0523185
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See declaration of conformity NSF/ANSI 169
Ambient temperature	0 °C ... 150 °C
Product weight	2.8 g
Pneumatic connection 1	Push-in sleeve Ø 4 mm
Pneumatic connection 2	Push-in sleeve Ø 4 mm
Note on materials	RoHS compliant
Housing material	Brass, chemically nickel-plated