

Pneumatic terminal LT-2-PK-3-DA

Part number: 5866

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Operating pressure | 0.1 bar ... 8 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 5.2 g |
| Pneumatic connection | Barbed connector PK-3 |
| Note on materials | RoHS compliant |