

# Pneumatic terminal LT-2-PK-4-DA

Part number: 5869

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Operating pressure	0.1 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	6 g
Pneumatic connection	Barbed fitting PK-4
Note on materials	RoHS-compliant