

Rod clevis SG-M12X1,25

Part number: 6145

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | M12x1.25 |
| Conforms to standard | ISO 8140 |
| Threaded connection | Internal thread M12x1.25 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 1.5 kN |
| Product weight | 166 g |
| Note on materials | RoHS-compliant |
| Bolt material | Steel Galvanized |
| Clevis material | Steel Galvanized |
| Nut material | Steel Galvanized |