

Distributor block FR-4-1/2-B

Part number: 6704

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal width | 18.6 mm |
| Mounting position | Any |
| Operating pressure for entire temperature range | 0 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 120 g |
| No. of outlets | 3 |
| No. of supply lines | 1 |
| Pneumatic connection 1 | Internal thread G1/2 |
| Pneumatic connection 2 | internal thread G1/2 |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast aluminum |