

Selector switch HW-6-38

Part number: 7199

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Valve function	8/6, bistable
Normal nominal flow rate (normalized to DIN 1343)	180 l/min
Pneumatic working port	M5
Operating pressure	0 bar ... 8 bar
Type of control	Direct
Symbol	00991542
Total leakage	1 l/h
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Nominal tightening torque	1.7 Nm
Tolerance for nominal tightening torque	± 10%
Pneumatic connection 1	M5
Pneumatic connection 2	M5