

Multi-plug KSV-16-B

Part number: 7559

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Nominal width | 4 mm |
| Operating pressure | -0.95 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 223 g |
| Max. connections | 16 |
| Pneumatic connection | PK-2 PK-3 PK-4 |
| Color | Gray |
| Note on materials | RoHS-compliant |