

Multi-socket KDVF-32-B

Part number: 7565

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	4 mm
Operating pressure	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	131 g
Max. connections	32
Pneumatic connection	PK-2 PK-3 PK-4
Color	Gray
Note on materials	RoHS-compliant