

Electrical adapter SASC-P4-A-M8-A

Part number: 8000326

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	straight, angled
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104 Diameter 8 mm, A-coded according to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Snap-locking Screw-type lock not rotatable
Electrical connection 1, type of mounting	Compatible with snap-locking Compatible with rotatable screw-type lock
Type of mounting	Threaded
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Material of screws	High-alloy steel