

Control cable NEBC-S1G25-K-3.2-N-LE25

Part number: 8001373

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Electrical connection	25-pin Straight plug/open end Sub-D / -
Shield	Yes
Cable length	3.2 m
Cable diameter	7 mm
Degree of protection	IP40 In mounted state
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 Zone III
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
Color cable sheath	Gray
Housing colour	Gray