

Manifold rail VABM-L1-18W-G38-5-G

Part number: 8004914

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 19 mm |
| Mounting position | Any |
| Max. no. of valve positions | 5 |
| Certification | c UL us - Recognized (OL) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Product weight | 1546 g |
| Pilot air port 12/14 | G1/8 |
| Pilot exhaust air port 82/84 | G1/8 |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | G1/4 |
| Pneumatic connection 3 | G3/8 |
| Pneumatic connection 4 | G1/4 |
| Pneumatic connection 5 | G3/8 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |