

Manifold rail VABM-L1-18W-G38-20-M-G

Part number: 8004925

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width dimension	19 mm
Mounting position	Any
Max. no. of valve positions	20
Certification	c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 60 °C
Product weight	4201 g
Pilot air port 12/14	G1/8
Pilot exhaust air port 82/84	G1/8
Pneumatic connection 1	G3/8
Pneumatic connection 2	G1/4
Pneumatic connection 3	G3/8
Pneumatic connection 4	G1/4
Pneumatic connection 5	G3/8
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy