

# Manifold rail VABM-L1-18W-G38-24-M-G

Part number: 8004926

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Width dimension                  | 19 mm                         |
| Mounting position                | Any                           |
| Max. no. of valve positions      | 24                            |
| Certification                    | c UL us - Recognized (OL)     |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L             |
| Storage temperature              | -20 °C ... 60 °C              |
| Product weight                   | 4909 g                        |
| Pilot air port 12/14             | G1/8                          |
| Pilot exhaust air port 82/84     | G1/8                          |
| Pneumatic connection 1           | G3/8                          |
| Pneumatic connection 2           | G1/4                          |
| Pneumatic connection 3           | G3/8                          |
| Pneumatic connection 4           | G1/4                          |
| Pneumatic connection 5           | G3/8                          |
| Note on materials                | RoHS-compliant                |
| Manifold rail material           | Wrought aluminum alloy        |