

Manifold block VABM-B10-25E-N12-2

Part number: 8026252

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 27.5 mm |
| Mounting position | Any |
| Max. no. of valve positions | 2 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 927 g |
| Type of mounting | With through-hole |
| Pilot air port 12 | 1/8 NPT |
| Pilot air port 14 | 1/8 NPT |
| Pneumatic connection 1 | 1/2 NPT |
| Pneumatic connection 3 | 1/2 NPT |
| Pneumatic connection 5 | 1/2 NPT |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |