


Manifold block VABM-B10-25S-N38-4

Part number: 8026272

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width dimension	27.5 mm
Mounting position	Any
Max. no. of valve positions	4
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	720 g
Type of mounting	With through-hole
Pneumatic connection 1	3/8 NPT
Pneumatic connection 3	3/8 NPT
Pneumatic connection 5	3/8 NPT
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy