

Duct separation VABD-S1-1-P1-C

Part number: 8029438

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Based on norm	ISO 5599-1
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Suitability for vacuum	yes
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-10 °C ... 50 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 50 °C
Product weight	60 g
Note on materials	RoHS-compliant
Separator plate material	Steel NBR