

Vertical pressure supply plate VMPA2-VSP-QS10

Part number: 8029489

FESTO



 General operating condition

Data sheet

Feature	Value
Width dimension	21 mm
Symbol	00991883
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	90 g
Pneumatic connection 1	QS-10
Note on materials	RoHS compliant
Supply plate material	PA-reinforced