

Elbow fitting NPFC-L-R34-G34-MF

Part number: 8030220

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--|
| Threaded fitting material | Brass, nickel-plated |
| Pack size | 10 |
| Operating pressure | -0.95 bar ... 50 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 150 °C |
| Product weight | 131.7 g |
| Pneumatic connection 1 | R3/4 |
| Pneumatic connection 2 | G3/4 |
| Note on materials | RoHS-compliant |