

# Elbow fitting NPFC-L-2R34-M

Part number: 8030227

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 150 °C
Product weight	102.6 g
Pneumatic connection 1	R3/4
Pneumatic connection 2	R3/4
Note on materials	RoHS-compliant