


X-fitting NPFC-X-R14-3G14-MFFF

Part number: 8030265

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:--]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 150 °C
Product weight	59.6 g
Pneumatic connection 1	R1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant