

Mounting NEAU-A-N8-2

Part number: 8032869

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	2
Design	for T-slot
Type of mounting	Clamped in T slot Lengthwise and crosswise to T-slot Can be inserted in slot from above
Ambient temperature	-25 °C ... 85 °C
Storage temperature	-25 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Housing material	PA-reinforced
Material of screws	High-alloy stainless steel
Slot nut material	Brass, nickel-plated